









COMPARATIF COMPRESSEURS

COMPRESSEUR	Page	Fonctionnement	Capacité (en kg)	Connectique	Entretien	Polyvalence	Sonorité	Utilisation		Simplicité d'Utilisation	Confort Patient	Budget	Moyenne
								Prévention	Soins				
NAUSIFLOW 2 COMPACT	122		120	SA	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,0
NAUSIFLOW 2S PLUS	123		150	CA	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4,2
NAUSIFLOW 2	126		130	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,2
NAUSIFLOW 2S	127		130	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,4
NAUSIFLOW 100 AUTO QUATTRO	128		150	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4,5
NAUSIFLOW 100 AUTO MAXI	129		300	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,9
NAUSIFLOW 2 COZINY	130		40	CZ	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,3
THERAFLO 3	131		280	TO	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	



AUTOMATIQUE



MÉCANIQUE

COMPARATIF MATELAS

MATELAS	Page	Largeur	Capacité (en kg)	Connectique	Entretien	Polyvalence	Résistance	Utilisation		Simplicité d'Utilisation	Confort Patient	Budget	Moyenne
								Prévention	Soins				
NAUSIFLOW 2 85 COMPACT	122	85	120	SA	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,2
NAUSIFLOW 2 80 COMPACT	122	80	120	SA	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3
NAUSIFLOW 2S-90	123	90	150	CA	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4
NAUSIFLOW 2-85 Compact RV Confort	124	85	120	RV	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4,3
NAUSIFLOW 2-90 RV Confort	125	90	150	RV	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4,5
NAUSIFLOW 2-90	126	90	150	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,9
NAUSIFLOW 2-70	126	70	150	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,9
NAUSIFLOW 2-100	127	100	150	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,9
NAUSIFLOW 2-120	127	120	150	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,9
NAUSIFLOW 100-512	128	80	150	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4
NAUSIFLOW 100-834	128	85	150	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4
NAUSIFLOW 100-834 ERGO	129	85	300	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4,5
NAUSIFLOW 100-834 120	129	120	300	PM	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,7
NAUSIFLOW 2 COZINY 100	130	36	3,5	CZ	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,2
NAUSIFLOW 2 COZINY 200	130	49	20	CZ	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,2
NAUSIFLOW 2 COZINY 300	130	70	40	CZ	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	3,2
THERAFLO 3-85/18	131	85	280	TO	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4,1
THERAFLO 3-90/20	131	90	280	TO	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	★★★★★	4,1